




Frequently Asked Questions

Precision 2000 Exit Trim



Various vandal resistant lever, knob and pull trims available.

Q: What is the Precision 2000?

A: The Precision 2000 is a heavy-duty grade 1 exit device. The Precision 2000 has a solid reputation for strength and reliability; all working mechanisms are encased in solid brass, bronze, aluminum or stainless steel housing incorporating true architectural finishes. The Precision 2100 rim type exit device successfully completed ten million operational cycles far exceeding the minimum 500,000 cycles required by Grade 1 standards.

Q: Who is the Precision 2000 customer?

A: The Precision 2000 is ideal for institutional applications such as educational, government and healthcare facilities.

Q: What device types is the Precision 2000 offered in?

A: The Precision 2000 is available in Rim (wide/narrow), SVR-Surface Vertical Rod, CVR-Concealed Vertical Rod (wide/narrow), wood door CVR and mortise types.

Q: Are mullions available to order for Precision 2000 double door rim applications?

A: The 822 & 811 Series mullions are available to order for these application types.

Q: Are there electrified options available for the Precision 2000?

A: There are 7 electrified options available to order on the Precision 2000 which includes Exit Alarm (ALK), Delayed Egress (DE), Door Position Monitoring Switch (DS), Electric Device (E), Electric Latch Retraction (ELR), Latchbolt Monitoring Switch (LS) and Touchbar Monitoring Switch (TS).

Q: What door thickness range can the Precision 2000 accommodate?

A: The Precision 2000 is standard to fit 1-3/4" – 2-1/4" thick doors. Thicker door options are available upon request.

Q: What door height range can the Precision 2000 accommodate?

A: The Precision 2000 SVR is available to order for 6' 8" - 10' doors.

Q: What door width range can the Precision 2000 accommodate?

A: The Precision 2000 can accommodate 2' 6" – 4' wide doors.

Q: What exit trims are available to order for the Precision 2000?

A: Vandal resistant lever, knob and pull trims are available to order for the Precision 2000. The vandal resistant lever does not require lever reset.

Q: What lever styles are offered for Precision 2000 trims?

A: The Precision 2000 has 4 standard lever style offerings (i.e., A, B, C & D). In addition, 20 decorative lever styles are available.

Q: Do you have to specify handing when ordering an Precision 2000?

A: You must specify handing when ordering an Precision 2000. However, most are field reversible.

Q: What keyways are available to order on the Precision 2000?

A: Cylinders are not included when you order Precision 2000 devices. They must be ordered separately. The Precision 2000 accommodates most manufacturers' rim and mortise cylinders.

Q: What finishes are offered for the Precision 2000?

A: The Precision 2000 is available in 7 finishes: 605, 606, 612, 613, 625, 628 and 630.

Q: What warranty does the Precision 2000 have?

A: The Precision 2000 has a 5 year mechanical warranty and a 1 year electrical warranty.

Q: What is the Barrier-Free (5 lb Push) option for Precision 2000?

A: The Barrier-Free option is a factory-configured enhancement that allows Precision 2000 Series exit devices to operate with a maximum 5 lb push force, supporting barrier-free and accessibility requirements in states such as California and Florida while maintaining Precision's durability and performance.

Q: Does the Barrier-Free option change the appearance of the exit device?

A: No. The Barrier-Free option does not change the appearance, trim compatibility, or low-profile design of the Precision 2000 Series.

Q: Which Precision exit devices are available with the Barrier-Free option?

A: The Barrier-Free (BF) option is available on Precision 2000 Series exit devices, including:

2100 Rim
2200 Surface Vertical Rod
2300 Mortise
2400 Narrow Stile Rim
2600 Narrow Stile Concealed Vertical Rod
2700 Wood Door Concealed Vertical Rod
2800 Metal Door Concealed Vertical Rod

Q: Does adding the Barrier-Free option affect durability or cycle performance?

A: No. Precision 2000 exit devices with the Barrier-Free option retain the same heavy-duty construction and long-term reliability expected from the PRECISION platform.

Q: Is the door prep for the Precision 2000 Barrier-Free device different than the door prep for a standard Precision 2000 device?

A: No, door preparation is identical for both Barrier-Free and standard devices.

DHW_1798_FAQ_EN BH 0526

For questions about ordering and to be sure you get the right configuration for your needs, [contact your BEST dormakaba sales representative](#).
6161 East 75th Street, Indianapolis, IN 46250 USA | [855-365-2407](tel:855-365-2407) | bestaccess.com | ONEdormakaba@dormakaba.com